



VE218L

Enclosure, vector, IP5x, 36Modules,version Austria

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 36

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 452 mm

Width of installed product 418 mm

Width in division units 18

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Connection

Number of conduit inlets

15

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

2

Quantity of section in width

1

Quantity of rails

2

Can be accessorized

Yes

Number of openings for flange plates

46

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

Standards

GWT Glow wire test

750 °C

European directive WEEE

concerned

Safety

IK protection code against mechanical impacts

07

Protection class

isol.class II

Use conditions

Operating temperature

-25...40 °C