



16417119

## Relay switch centre plate for hotel card, K.1, p. white glossy

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Configuration

Switch mode 1pole

Antibacterial treatment No

#### Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

#### Electric current

Inductive load at  $\cos \varphi = 0.6$  max. 6 A

Switching current 10 A /230 V AC1

#### Dimensions

Depth 58.6 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

#### Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

#### Materials

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

#### Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

#### LED control

LED illuminated with blue LED if hotel card is not inserted

---

**Incandescent bulbs control**

---

230 V incandescent lamps and halogen lamps

1500 W

---

**Installation, mounting**

---

Installation mode

with spreader claws

---

**Connection**

---

Screw terminals (max.)

2 x 2,5 mm<sup>2</sup>

Type of connection

with screw-in lift terminals

---

**Settings**

---

Delay time incrementally adjustable

0, 15, 30, 60 s

Setting

with potentiometer for incremental adjustment of delay time

---

**Equipment**

---

Lighting

for illumination

Potential-free

with potential-free contact

---

**Use cases**

---

Application

Light control, Hotel application

---

**Safety**

---

Protection index IP

IP20

---

**Use conditions**

---

Operating temperature

-5...50 °C

Storage/transport temperature

-25...70 °C (storage at > 45°C reduces the service life)

---

**Identification**

---

Application, usage

Light control

Main design line

Berker K.1