



VE218PN

**Enclosure, vector, surface mounted, IP65, 36M, UV stable, with metric cable entry**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 36

**Compatibility**

Suitable for Multimedia No

**Main electrical features**

Nominal voltage 400 V

**Voltage**

Rated operational voltage in DC 1000 V DC

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 452 mm

Width of installed product 418 mm

Width in division units 18

Thickness of sidewall material 2.5 mm

**Cover, door**

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

#### Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

#### Connection

Number of conduit inlets	15
--------------------------	----

#### Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

#### Equipment

Number of rows	2
Quantity of section in width	1
Quantity of rails	2
Can be accessorized	Yes
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C

#### Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------