



16417134

Relay switch centre plate for hotel card, K.1, al., matt, lacq.

Technical characteristics

Architecture

Fixing mode flush-mounting

Configuration

Switch mode 1pole

Antibacterial treatment No

Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$ max. 6 A

Switching current 10 A /230 V AC1

Dimensions

Depth 58.6 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Materials

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

LED control

LED

illuminated with blue LED if hotel card is not inserted

Incandescent bulbs control

230 V incandescent lamps and halogen lamps

1500 W

Installation, mounting

Installation mode

with spreader claws

Connection

Screw terminals (max.)

2 x 2,5 mm²

Type of connection

with screw-in lift terminals

Settings

Delay time incrementally adjustable

0, 15, 30, 60 s

Setting

with potentiometer for incremental adjustment of delay time

Equipment

Lighting

for illumination

Potential-free

with potential-free contact

Use cases

Application

Light control, Hotel application

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...50 °C

Storage/transport temperature

-25...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage

Light control

Main design line

Berker K.5