



VE312F

Enclosure,vector,IP5x,36M

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 36

Compatibility

Suitable for Multimedia No

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 552 mm

Width of installed product 310 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification od protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment

untreated

Installation, mounting

Suitable for outdoor use

No

Connection

Number of conduit inlets

12

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

3

Quantity of section in width

1

Number of keys

1

Quantity of rails

3

Can be accessorized

Yes

Number of openings for flange plates

46

Extension possible

No

Earthing terminal block

Yes

Neutral terminal block

No

Signal passing door

Yes

Standards

GWT Glow wire test

750 °C

European directive WEEE

concerned

Safety

Protection class

isol.class II

REACH conform

No

RoHS conform

Yes

Halogen free

No

Use conditions

Operating temperature

-25...40 °C