



VE312SN

Enclosure,vector,surface mounted,IP65,36M,UV stable,without cable entry

Technical properties

Architecture

Fixing mode surface-mounting

Functions

Concurrently switching N-neutral Yes

With a pipe-in lead Yes

Configuration

Number of modules 36

Main electrical features

Nominal voltage 400 V

Voltage

Rated operational voltage in DC 1000 V DC

Electric current

Rated current 63 A

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 552 mm

Width of installed product 310 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

Colour light grey

RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	Yes
Connection	
Number of conduit inlets	12
Settings	
Enclosure type	Distributor empty cabinet
Scope of delivery	
With cover	Yes
Equipment	
Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	46
Extension possible	No
Signal passing door	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
Use conditions	
Operating temperature	-25...40 °C