



VE318SN

Enclosure,vector,surface mounted, IP65,54M,UV stable,without cable entry

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	54
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	151 mm
----------------------------	--------

Internal depth	151 mm
----------------	--------

Height of installed product	602 mm
-----------------------------	--------

Width of installed product	418 mm
----------------------------	--------

Width in division units	18
-------------------------	----

Thickness of sidewall material	2.5 mm
--------------------------------	--------

Cover, door

Identification of protection index	65
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	Yes
---------------------------	-----

Materials

Colour	light grey
--------	------------

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Material	Polycarbonate (PC)
----------	--------------------

Subject to technical modifications

Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	Yes
Connection	
Number of conduit inlets	15
Equipment	
Number of rows	3
Quantity of section in width	1
Number of keys	1
Quantity of rails	3
Can be accessorized	Yes
Extension possible	No
Signal passing door	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
REACH conform	No
RoHS conform	Yes
Use conditions	
Operating temperature	-25...40 °C