



VS108TJ



**Small distributor,golf,surface,1row,IP40,8M,MS-terminal,N+PE,transparent door**

#### Technical properties

##### Architecture

Fixing mode surface-mounting

##### Functions

With a pipe-in lead Yes

##### Configuration

Number of modules 8

##### Main electrical features

Nominal voltage 400 V

##### Electric current

Rated current 63 A

##### Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 184 mm

Width of installed product 210 mm

Width in division units 8

##### Cover, door

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

##### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

##### Installation, mounting

Suitable for outdoor use No

**Equipment**

|                                      |     |
|--------------------------------------|-----|
| Number of rows                       | 1   |
| Quantity of section in width         | 1   |
| Quantity of rails                    | 1   |
| Can be accessorized                  | Yes |
| Number of openings for flange plates | 0   |
| Extension possible                   | Yes |
| Earthing terminal block              | Yes |
| Neutral terminal block               | Yes |
| Signal passing door                  | Yes |

**Standards**

|                         |           |
|-------------------------|-----------|
| GWT Glow wire test      | 650 °C    |
| European directive WEEE | concerned |

**Safety**

|   |               |
|---|---------------|
| IK protection code against mechanical impacts | 07            |
| Protection class                              | isol.class II |
| REACH conform                                 | Yes           |
| RoHS conform                                  | Yes           |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|