



VS118PF

**Small distributor,golf,surface,1row,IP40,18M,MS-terminal,PE,white door**

#### Technical properties

##### Architecture

|             |                  |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

##### Functions

|                     |     |
|---------------------|-----|
| With a pipe-in lead | Yes |
|---------------------|-----|

##### Configuration

|                   |    |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

##### Main electrical features

|                 |       |
|-----------------|-------|
| Nominal voltage | 400 V |
|-----------------|-------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

##### Dimensions

|                             |        |
|-----------------------------|--------|
| Depth of installed product  | 99 mm  |
| Internal depth              | 99 mm  |
| Height of installed product | 252 mm |
| Width of installed product  | 390 mm |
| Width in division units     | 18     |

##### Cover, door

|                                    |                |
|------------------------------------|----------------|
| Identification od protection index | 40             |
| Interlockable                      | No             |
| Number of keylock of the door      | 0              |
| Cover type                         | Closed (plain) |
| Door locking                       | without        |
| Door leave                         | single         |
| Cover type                         | Door           |
| Transparent cover or door          | No             |

##### Materials

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Material                  | plastic               |
| Type of surface treatment | untreated             |

##### Installation, mounting

|                          |    |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

**Equipment**

|                                      |     |
|--------------------------------------|-----|
| Number of rows                       | 1   |
| Quantity of section in width         | 1   |
| Quantity of rails                    | 1   |
| Can be accessorized                  | Yes |
| Number of openings for flange plates | 0   |
| Extension possible                   | Yes |
| Earthing terminal block              | Yes |
| Neutral terminal block               | No  |
| Signal passing door                  | Yes |

**Standards**

|                         |               |
|-------------------------|---------------|
| GWT Glow wire test      | 650 °C        |
| European directive WEEE | not concerned |

**Safety**

|                                               |               |
|-----------------------------------------------|---------------|
| IK protection code against mechanical impacts | 07            |
| Protection index IP                           | IP40          |
| Protection class                              | isol.class II |
| REACH conform                                 | No            |
| RoHS conform                                  | Yes           |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|