



VU12NE

Encl.,Volta,flush,1x12MOD,IP30,Version NCEE

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	12
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Insertion depth	89 mm
Depth of installed product	98 mm
Internal depth	91.5 mm
Height of installed product	356 mm
Installation height	321 mm
Length	356 mm
Width of installed product	348 mm
Width in division units	12
Thickness of sidewall material	2.5 mm
Built-in height	340 mm
Built-in width	314.5 mm

Cover, door

Identification of protection index	30
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Type of surface treatment

untreated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Scope of delivery

With cover No

Equipment

Number of units 12

Number of rows 1

Quantity of rails 1

Can be accessorized Yes

Number of openings for flange plates 0

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block No

Signal passing door No

Standards

GWT Glow wire test 650 °C

Protection class according to IEC-61140 II

Safety

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform No

Halogen free No

Impact strength IK05

Use conditions

Operating temperature -40...40 °C