



20262089

**Thermostat, change-over contact, centre plate, R.1/R.3, p. white glossy**

**Technical characteristics**

**Functions**

With cooling function Yes

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

**Electric current**

Switching current "Heating" at  $\cos \varphi = 0.6$  4 A

Heating switching current 10 A

"Switching current ""Cooling"" at  $\cos \varphi = 0.6$ " 2 A

"Switching current ""Cooling""" 5 A

**Measurement**

Range of temperatures 5 / 30 °C

**Materials**

Colour of design line polar white

Colour polarwhite

Material Plastic/metal

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Type of connection with screw terminals

**Equipment**

Switching temperature difference  $\approx 0.5$  K

Heating for heating or cooling mode

Control setting knob with temperature range limitation

Valve drives e.g. for valve drives closed in de-energised state

**Use conditions**

Energy efficiency class I (1%)

**temperatur**

Temperature 5...30 °C

**Identification**

Application, usage

HVAC control

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1, Berker R.3, Berker R.8

---

**Instructions**

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!