



VU36NE

Encl.,Volta,flush,3x12MOD,IP30,Version NCEE

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Number of modules 36

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Insertion depth 89 mm

Depth of installed product 98 mm

Internal depth 91.5 mm

Height of installed product 630.5 mm

Installation height 595 mm

Length 630.5 mm

Width of installed product 348 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Built-in height 615 mm

Built-in width 314.5 mm

Cover, door

Identification of protection index 30

Interlockable No

Number of keylock of the door 0

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment

untreated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Scope of delivery

With cover No

Equipment

Number of units 12

Number of rows 3

Quantity of rails 3

Can be accessorized Yes

Number of openings for flange plates 0

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block No

Signal passing door No

Standards

GWT Glow wire test 650 °C

Protection class according to IEC-61140 II

Safety

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform No

Halogen free No

Impact strength IK05

Use conditions

Operating temperature -40...40 °C