



VZ131N

**Door, Volta, flush/Hollow wall, transparent, 1 rows**

**Technical properties**

**Architecture**

|                        |      |
|------------------------|------|
| Intended door position | left |
|------------------------|------|

**Compatibility**

|                             |                             |
|-----------------------------|-----------------------------|
| Suitable for enclosure type | Hollow wall ; Flush mounted |
|-----------------------------|-----------------------------|

**Dimensions**

|                             |          |
|-----------------------------|----------|
| Depth of installed product  | 36 mm    |
| Height of installed product | 296.5 mm |
| Width of installed product  | 288 mm   |
| Built-in height             | 296.5 mm |
| Built-in width              | 288 mm   |

**Cover, door**

|                               |        |
|-------------------------------|--------|
| Material thickness cover      | 1 mm   |
| Number of keylock of the door | 0      |
| Door leave                    | single |
| Transparent cover or door     | Yes    |

**Materials**

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | white                 |
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Material                  | plastic               |
| Type of surface treatment | untreated             |

**Installation, mounting**

|                          |    |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

**Equipment**

|                |   |
|----------------|---|
| Number of rows | 1 |
|----------------|---|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|   |      |
|---|------|
| IK protection code against mechanical impacts | IK05 |
| REACH conform                                 | No   |
| RoHS conform                                  | Yes  |