



20266089

Thermostat, change-over contact, centre plate, Q.x, p. white velvety

Technical characteristics

Functions

With cooling function No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Switching current "Heating" at $\cos \varphi = 0.6$ 4 A

Heating switching current 10 A

"Switching current ""Cooling"" at $\cos \varphi = 0.6$ " 2 A

"Switching current ""Cooling"""" 5 A

Measurement

Range of temperatures 5 / 30 °C

Materials

Colour of design line polar white

Installation, mounting

Installation mode without spreader claws

Connection

Type of connection with plug-in terminals

Equipment

Switching temperature difference ≈ 0.5 K

Heating for heating or cooling mode

Control setting knob with temperature range limitation

Valve drives e.g. for valve drives closed in de-energised state

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Energy efficiency class I (1%)

temperatur

Identification

Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
