



20306084

therm. w. NC cont., Centre pl., rocker switch a. LED, Q.x, alu velvety, lacq.

#### Technical characteristics

#### Functions

Switching with on/off switch and indicator LED for "on"

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

#### Electric current

Inductive load at $\cos \varphi = 0.6$	max. 4 A
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
Switching current	10 A

#### Dimensions

Insertion depth	24.5 mm
-----------------	---------

#### Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

#### Materials

Colour	aluminium
Material / workmanship	lacquered
Material	Plastic/metal

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

#### Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

#### Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

**Use conditions**

---

Energy efficiency class	I (1%)
-------------------------	--------

**temperatur**

---

Temperature	5...30 °C
-------------	-----------

**Identification**

---

Application, usage	HVAC control
--------------------	--------------

---

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

---

Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	--