



20306086

**Thermostat, NC contact, centre plate, rocker switch, Q.1/Q.3, ant. velvety lacq.**

#### Technical characteristics

#### Functions

|                       |   |
|-----------------------|---|
| Switching             | with on/off switch and indicator LED for "on" |
| With cooling function | Yes   |

#### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |

#### Electric current

|   |          |
|---|----------|
| Inductive load at $\cos \varphi = 0.6$              | max. 4 A |
| Switching current "Heating" at $\cos \varphi = 0.6$ | 4 A      |
| Heating switching current                           | 10 A     |
| Switching current                                   | 10 A     |

#### Dimensions

|                 |         |
|-----------------|---------|
| Insertion depth | 24.5 mm |
|-----------------|---------|

#### Measurement

|                       |           |
|-----------------------|-----------|
| Range of temperatures | 5 / 30 °C |
|-----------------------|-----------|

#### Materials

|                        |               |
|------------------------|---------------|
| Colour of design line  | anthracite    |
| Colour                 | anthracite    |
| Material / workmanship | lacquered     |
| Material               | Plastic/metal |

#### Installation, mounting

|                   |                        |
|-------------------|------------------------|
| Installation mode | without spreader claws |
|-------------------|------------------------|

#### Connection

|                    |   |
|--------------------|---|
| Type of connection | with plug-in terminals                      |
| Connection         | with separate connection for night lowering |

#### Equipment

|                                  |  |
|----------------------------------|--|
| Night lowering                   | ≈ 4 K  |
| Switching temperature difference | ≈ 0.5 K  |
| Control                          | setting knob with temperature range limitation     |
| Valve drives                     | e.g. for valve drives closed in de-energised state |

#### Use

**Use conditions**

---

|                         |        |
|-------------------------|--------|
| Energy efficiency class | I (1%) |
|-------------------------|--------|

**temperatur**

---

|             |           |
|-------------|-----------|
| Temperature | 5...30 °C |
|-------------|-----------|

**Identification**

---

|                    |              |
|--------------------|--------------|
| Application, usage | HVAC control |
|--------------------|--------------|

---

|                  |                        |
|------------------|------------------------|
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
|------------------|------------------------|

---

|                          |  |
|--------------------------|--|
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |
|--------------------------|--|