



WE053T



## Automatic switch Essensya 3 wires Titane

### Technical properties

#### Architecture

Fixing mode flush-mounting

#### Functions

Remote operation No

With switch function No

#### Main electrical features

Frequency 50/60 Hz

#### Detection

Detection angle 180 °

Sensor type detector of movement

Frontal detecting distance 12 m

Side detecting distance 8 m

#### Materials

Material plastic

Surface appearance matt

Type of surface treatment untreated

#### Lighting control

Photocell sensitivity 5 / 1000 Lux

#### Settings

Delay ON 0 s

Delay OFF 0 s

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -5...45 °C