



20316086

Temp. cont., NC contact, Cen. plate, 24V AC/DC, rocker switch, Q.1/Q.3, ant. velv. lacq.

#### Technical characteristics

#### Functions

Switching with on/off switch and indicator LED for "on"

#### Main electrical features

Nominal voltage	24 V
Rated voltage	24 V AC/DC
Frequency	50/60 Hz

#### Electric current

Switching current	10 A~/4 A=
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A

#### Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

#### Materials

Colour of design line	anthracite
Colour	anthracite
Material / workmanship	lacquered
Material	Plastic/metal

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

#### Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

#### Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes

<b>Use conditions</b>	
Energy efficiency class	I (1%)
<b>temperatur</b>	
Temperature	5...30 °C
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9