



WE250

TV socket direct Essensya Pure

Technical properties

Architecture

| | |
|------|----|
| Type | TV |
|------|----|

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

Connectivity

| | |
|----------|-------------|
| Passband | 4 - 862 MHz |
|----------|-------------|

Dimensions

| | |
|----------------------------|-------|
| Depth of installed product | 32 mm |
|----------------------------|-------|

| | |
|-----------------------------|-------|
| Height of installed product | 75 mm |
|-----------------------------|-------|

| | |
|----------------------------|-------|
| Width of installed product | 75 mm |
|----------------------------|-------|

Attenuation

| | |
|----------------------|------|
| Tap loss at 2150 MHz | 1 dB |
|----------------------|------|

| | |
|---------------------|------|
| Tap loss at 860 MHz | 1 dB |
|---------------------|------|

Materials

| | |
|--------|-------|
| Colour | white |
|--------|-------|

Equipment

| | |
|-------------------|---|
| Number of outputs | 1 |
|-------------------|---|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 01 |
|---|----|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|----|
| Halogen free | No |
|--------------|----|

| | |
|-----------------|------|
| Impact strength | IK01 |
|-----------------|------|

Identification

| | |
|-------|----------|
| Range | essensya |
|-------|----------|