



WNA020

cubyko Push-button 1F composable grey IP55

Technical properties

Architecture

| | |
|----------------------|-------------|
| Type of control unit | Push button |
| Number of keys | 1 |
| Fixing mode | Clipped |

Controls and indicators

| | |
|----------------|----|
| Indicator lamp | no |
|----------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Dimensions

| | |
|---|-------|
| Installation depth, flush-mounted boxes | 40 mm |
| Depth of installed product | 40 mm |
| Height of installed product | 75 mm |
| Width of installed product | 75 mm |

Materials

| | |
|----------|---------------|
| Material | polypropylène |
|----------|---------------|

Installation, mounting

| | |
|---------------|---------------------------------|
| Fixing type | turn screw lock |
| Mounting type | flush mounted / surface mounted |

Connection

| | |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm ² - maxi 2x2,5 mm ² |
| Type of contacts | 1NO |
| Type of connection | Quickconnect |

Standards

| | |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 07 |
| Impact strength | IK07 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -15...30 °C |
| Storage/transport temperature | -50...50 °C |

Identification

| | |
|-------------|-----------------------------|
| Range | cubyko |
| Composition | Mechanism with upper casing |