



20441909

**Thermostat, NO contact, centre plate, time-contr., S.1/B.3/B.7, p.white m. plas.**

#### Technical characteristics

#### Functions

Function	Operating hours meter or energy consumption display adjustable ; timer for changing the temperature by the hour ; with access protection ; with frost protection function ; with valve protection function
Slide switch	with switchover manual/automatic mode
With cooling function	Yes

#### Controls and indicators

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

#### Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

#### Electric current

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

#### Dimensions

Insertion depth	25 mm
-----------------	-------

#### Power

Power consumption	$\approx 1.2$ W
-------------------	-----------------

#### Battery

Lithium cell power reserve [years]	$\approx 10$
------------------------------------	--------------

#### Detection

Sensor	with integrated temperature sensor
--------	------------------------------------

#### Materials

Colour of design line	polar white
-----------------------	-------------

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

Connection	with additional connection for external floor temperature sensor/remote sensor
<b>Settings</b>	
Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	programmable with operating unit removed ; 3 preset time programmes, individually adjustable ; 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun ; max. 9 switching times per weekday
Time	with automatic summer-/winter time switching (can be switched off)
<b>Equipment</b>	
Switching temperature difference	≈ 0.5 K
Heating	with self-teaching heating curve ; for underfloor heating control using room and/or floor temperature possible ; for heating or cooling mode ; for room and floor heaters
Control	control process PWM or 2-point (on/off) can be selected ; PWM cycle time and hysteresis (for two-point control) settable
Valve drives	type of actuator (currentless closed/open) adjustable
<b>Use</b>	
Differentiation characteristic 2 - Sales	Time-controlled
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7