



WNE040B

cubyko 2-gang 2-way switch flush mounted white IP55

Technical properties

Architecture

| | |
|----------------------|---------------|
| Type of order | Switch |
| Type of control unit | double rocker |

Configuration

| | |
|-------------|-------|
| Switch mode | 2 way |
|-------------|-------|

Controls and indicators

| | |
|----------------|-----------------|
| Indicator lamp | as an accessory |
| Push-buttons | No |

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 40 mm |
| Height of installed product | 75 mm |
| Dimensions (LLxwwxhh) | 83X83X37 |
| Width of installed product | 75 mm |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
| Material | polypropylène |

Installation, mounting

| | |
|---------------|-------|
| Mounting type | flush |
|---------------|-------|

Connection

| | |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm ² - maxi 2x2,5 mm ² |
| Type of contacts | 2 way |
| Type of connection | Quickconnect |

Equipment

| | |
|----------|--|
| Lighting | without lighting (cannot be illuminated) |
|----------|--|

| | |
|----------------|----|
| Heating switch | No |
|----------------|----|

Standards

| | |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 07 |
|---|----|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|-----------------|------|
| Impact strength | IK07 |
|-----------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15...30 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -50...50 °C |
|-------------------------------|-------------|

Identification

| | |
|-------|--------|
| Range | cubyko |
|-------|--------|

| | |
|-------------|-----------------------------|
| Composition | Mechanism with upper casing |
|-------------|-----------------------------|