



20447106

**Thermostat, NO contact, centre plate, time-controlled, K.1, ant., matt**

**Technical characteristics**

**Functions**

Function	with valve protection function, Operating hours meter or energy consumption display adjustable, with access protection, with frost protection function, timer for changing the temperature by the hour
Slide switch	with switchover manual/automatic mode

**Controls and indicators**

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

**Electric current**

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

**Dimensions**

Insertion depth	25 mm
-----------------	-------

**Power**

Power consumption	≈ 1.2 W
-------------------	---------

**Battery**

Lithium cell power reserve [years]	≈ 10
------------------------------------	------

**Detection**

Sensor	with integrated temperature sensor
--------	------------------------------------

**Materials**

Colour of design line	anthracite
Colour	anthracite
Material	Plastic/metal

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Type of connection	with screw terminals
--------------------	----------------------

Connection	with additional connection for external floor temperature sensor/remote sensor
<b>Settings</b>	
Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	max. 9 switching times per weekday, 3 preset time programmes, individually adjustable, programmable with operating unit removed, 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun
Time	with automatic summer-/winter time switching (can be switched off)
<b>Equipment</b>	
Switching temperature difference	≈ 0.5 K
Heating	for heating or cooling mode, with self-teaching heating curve, for underfloor heating control using room and/or floor temperature possible, for room and floor heaters
Control	PWM cycle time and hysteresis (for two-point control) settable, control process PWM or 2-point (on/off) can be selected
Valve drives	type of actuator (currentless closed/open) adjustable
<b>Use</b>	
Differentiation characteristic 2 - Sales	Time-controlled
<b>Use conditions</b>	
Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker K.1