



WNE040B

cubyko 2-gang 2-way switch flush mounted white IP55

Technical properties

Architecture

| | |
|----------------------|---------------|
| Type of control unit | double rocker |
| Fixing mode | Screwed |

Controls and indicators

| | |
|--------------|----|
| Push-buttons | No |
|--------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 40 mm |
| Height of installed product | 75 mm |
| Dimensions (LLxwxhh) | 83X83X37 |
| Width of installed product | 75 mm |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

Connection

| | |
|--------------------|--------------|
| Type of connection | Quickconnect |
|--------------------|--------------|

Equipment

| | |
|----------------|--|
| Lighting | without lighting (cannot be illuminated) |
| Heating switch | No |

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 07 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Impact strength | IK07 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -15...30 °C |
| Storage/transport temperature | -50...50 °C |