



20447109

**Thermostat, NO contact, centre plate, time-controlled, K.1, p. white glossy**

**Technical characteristics**

**Functions**

Function	Operating hours meter or energy consumption display adjustable ; timer for changing the temperature by the hour ; with valve protection function ; with access protection ; with frost protection function
Slide switch	with switchover manual/automatic mode
With cooling function	Yes

**Controls and indicators**

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

**Electric current**

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

**Dimensions**

Insertion depth	25 mm
-----------------	-------

**Power**

Power consumption	$\approx 1.2$ W
-------------------	-----------------

**Battery**

Lithium cell power reserve [years]	$\approx 10$
------------------------------------	--------------

**Detection**

Sensor	with integrated temperature sensor
--------	------------------------------------

**Materials**

Colour of design line	polar white
-----------------------	-------------

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Type of connection	with screw terminals
--------------------	----------------------

Connection	with additional connection for external floor temperature sensor/remote sensor
<b>Settings</b>	
Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	3 preset time programmes, individually adjustable ; programmable with operating unit removed ; 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun ; max. 9 switching times per weekday
Time	with automatic summer-/winter time switching (can be switched off)
<b>Equipment</b>	
Switching temperature difference	≈ 0.5 K
Heating	for room and floor heaters ; with self-teaching heating curve ; for underfloor heating control using room and/or floor temperature possible ; for heating or cooling mode
Control	control process PWM or 2-point (on/off) can be selected ; PWM cycle time and hysteresis (for two-point control) settable
Valve drives	type of actuator (currentless closed/open) adjustable
<b>Use</b>	
Differentiation characteristic 2 - Sales	Time-controlled
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker K.1