



WUZ672



kallystx Ceiling loudspeaker 2"

Technical properties

Functions

Loudness control	No
------------------	----

Dimensions

Insertion depth	35 mm
Depth of installed product	29 mm
Internal depth	29 mm
Installation opening Ø	68 mm
Recommended installation height	2.4...4 m
Installation wall thickness	15 mm
Loudspeaker chassis Ø	51 mm

Frequency

Frequency range audio	200 Hz...16 kHz
Frequency band	200 / 16000 Hz
Frequency response (-3 dB)	200...16000 Hz

Resistance

Impedance	20 Ω
-----------	------

Detection

- at 1 kHz	180 °
- at 4 kHz	120 °
- at 8 kHz	140 °

Materials

Colour	white
Material	metal

Installation, mounting

Built-in	Yes
Mounting Method	Surface

Connection

Conductor cross-section (flexible)	max. 1.5 mm ²
Type of connection	with screw terminal

Equipment

Sound pressure level 1 W/1 m	82 dB
Sound pressure level at rated power	87 dB

Identification

Main design line

Communication technology

Instructions

Information text

Housing screws made of stainless steel.