



281901

Rotary dimmer house electronics

Technical characteristics

Architecture

Type of control unit Rotative

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fine-wire fuse T 1.6 H 250

Fuse short-circuit and overload proof (fine-wire fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Loss power at full load ≈ 4 W

Materials

Colour not applicable

Material Plastic/metal

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 60...400 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load Resistive load

Type of connection with screw terminals

Equipment

Dimming principle phase cut-on

Switches / socket outlets with rotary on/off switch

Use

Use conditions

Operating temperature	5...25 °C
-----------------------	-----------

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------

Secondary design line(s)	House electronics
--------------------------	-------------------

Instructions

Information text	Possible to change fuse without removing cover.
------------------	---