



WXF421N

**Socket for trunking gallery 2P+E 16A night**

**Technical properties**

**Architecture**

|               |        |
|---------------|--------|
| Type of order | Socket |
| Type of pole  | 2P+T   |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

**Main electrical features**

|                 |       |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 45 mm   |
| Height | 43.5 mm |
| Width  | 67.5 mm |

**Cover, door**

|       |                  |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

**Materials**

|                    |              |
|--------------------|--------------|
| Surface appearance | satın finish |
|--------------------|--------------|

**Connection**

|   |   |
|---|---|
| Connection cross-sect. flexible conductor | 1,5 / 2,5mm <sup>2</sup>                              |
| Connection cross-sect. rigid cable        | mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup> |
| Type of connection                        | Quickconnect  |

**Equipment**

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

**Standards**

|           |           |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

**Safety**

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 07                          |
| REACH conform                                 | Yes                         |
| RoHS conform                                  | Yes                         |
| Protection                                    | Enhanced contact protection |

**Use conditions**

---

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

**Identification**

---

Composition

Mechanism with upper casing