



28198989

**Rot. dimmer cover plate, setting knob, S.1, p. white glossy**

**Technical characteristics**

**Architecture**

Type of control unit Rotative

**Functions**

Soft startup bulb-preserving soft startup

**Main electrical features**

Nominal voltage 230 V

Frequency 50 Hz

**Voltage**

Operating voltage 230 V AC

**Fuse**

Fuse short-circuit and overload proof (fine-wire fuse)

**Dimensions**

Axis dimension Ø 4 mm

**Power**

Loss power at full load ≈ 4 W

**Materials**

Colour of design line polar white

Colour polarwhite

Material duroplastic

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps 60...400 W

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Type of load Resistive load

Type of connection with screw terminals

**Equipment**

Dimming principle phase cut-on

Switches / socket outlets with rotary on/off switch

**Use**

Differentiation characteristic 2 - Sales	Setting knob
Differentiation characteristic 3 - Sales	with soft-lock
<b>Use conditions</b>	
Operating temperature	5...25 °C
<b>Identification</b>	
Application, usage	Light control
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7