



28199939

Rot. dimmer cover plate, setting knob, S.1, al., matt, lacq.

Technical characteristics

Architecture

Type of control unit	Rotative
----------------------	----------

Functions

Soft startup	bulb-preserving soft startup
--------------	------------------------------

Main electrical features

Nominal voltage	230 V
-----------------	-------

Frequency	50 Hz
-----------	-------

Voltage

Operating voltage	230 V AC
-------------------	----------

Fuse

Fuse	short-circuit and overload proof (fine-wire fuse)
------	---

Dimensions

Axis dimension Ø	4 mm
------------------	------

Power

Loss power at full load	≈ 4 W
-------------------------	-------

Materials

Colour	aluminium
--------	-----------

Material / workmanship	lacquered
------------------------	-----------

Material	thermoplastic
----------	---------------

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	60...400 W
--	------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of load	Resistive load
--------------	----------------

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Dimming principle	phase cut-on
-------------------	--------------

Switches / socket outlets	with rotary on/off switch
---------------------------	---------------------------

Use

Subject to technical modifications

Differentiation characteristic 2 - Sales	Setting knob
Differentiation characteristic 3 - Sales	with soft-lock
Use conditions	
Operating temperature	5...25 °C
Identification	
Application, usage	Light control
Main design line	Berker S.1
Secondary design line(s)	House electronics