



WXF421N

## Socket for trunking gallery 2P+E 16A night

### Technical properties

#### Architecture

|               |           |
|---------------|-----------|
| Type of order | Socket    |
| Type of pole  | 2P+T      |
| Fixing mode   | Wall duct |

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

#### Main electrical features

|                 |       |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

#### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

#### Dimensions

|        |         |
|--------|---------|
| Depth  | 45 mm   |
| Height | 43.5 mm |
| Width  | 67.5 mm |

#### Cover, door

|       |                  |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

#### Materials

|                           |                      |
|---------------------------|----------------------|
| Colour                    | deep black           |
| RAL colour                | RAL 9005 - Jet black |
| Material                  | Polycarbonate (PC)   |
| Surface appearance        | satın finish         |
| Type of surface treatment | Painted              |

#### Connection

|                                           |                                                       |
|-------------------------------------------|-------------------------------------------------------|
| Connection cross-sect. flexible conductor | 1,5 / 2,5mm <sup>2</sup>                              |
| Connection cross-sect. rigid cable        | mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup> |
| Type of connection                        | Quickconnect                                          |

#### Equipment

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

#### Standards

|                         |           |
|-------------------------|-----------|
| Approvals               | NFC 61314 |
| European directive WEEE | concerned |

**Safety**

---

IK protection code against mechanical impacts 07

Protection index IP IP20

Protection Enhanced contact protection

**Use conditions**

---

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

---

Composition Mechanism with upper casing