



WXF422T

Double socket for trunking gallery 2P+E 16A titane

Technical properties

Architecture

| | |
|--------------|------|
| Type of pole | 2P+T |
|--------------|------|

Configuration

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|-------|-------|
| Depth | 45 mm |
|-------|-------|

| | |
|--------|---------|
| Height | 42.5 mm |
|--------|---------|

| | |
|-------|-------|
| Width | 90 mm |
|-------|-------|

Cover, door

| | |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

Materials

| | |
|------------------------------|--------|
| Free area for finishing name | titane |
|------------------------------|--------|

| | |
|--------|------------------|
| Colour | aluminium optics |
|--------|------------------|

| | |
|------------|----------------------------|
| RAL colour | RAL 9006 - White aluminium |
|------------|----------------------------|

| | |
|---------------------------|---------|
| Type of surface treatment | Painted |
|---------------------------|---------|

Connection

| | |
|--------------------|--------------|
| Type of connection | Quickconnect |
|--------------------|--------------|

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 07 |
|---|----|

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Protection

Enhanced contact protection

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Composition

Mechanism with upper casing