



283410

## Rot. dimmer centre plate (R, L, C), soft-lock, 1930/glass, p. white glossy

### Technical characteristics

#### Architecture

Type of control unit Push & rotative

#### Functions

Soft startup bulb-preserving soft startup

#### Main electrical features

Nominal voltage 230 V

#### Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Dimensions

Axis dimension Ø 4 mm

#### Power

Dimmable conventional transformers 50...420 VA

connected load 50...420 W/VA

Loss power at full load ≈ 5 W

Electronic transformers 50...420 W

#### Measurement

Extension unit input with input for extension units insert for universal rotary dimmer

#### Materials

Colour of design line polar white

Colour polarwhite

Material Plastic/metal

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps 50...420 W

#### Installation, mounting

Installation mode for screw fastening

#### Connection

Type of load universal

Type of connection	with plug-in terminals
<b>Scope of delivery</b>	
Component	with incremental encoder
<b>Equipment</b>	
Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise
Brightness	with brightness memory
<b>Use</b>	
Differentiation characteristic 3 - Sales	Soft-lock
<b>Use conditions</b>	
Operating temperature	5...25 °C
<b>Identification</b>	
Release issue	2
Secondary design line(s)	Serie 1930, Serie 1930 Porzellan Made by Rosenthal, Serie Glass, Series R.classic
<b>Instructions</b>	
Information text	Trouble-free operation will be obtained only with Berker TronicÂ® transformers.