



XEV201C

**EV charging station witty park 1x7kW 1P M3T2S M2TE IP54 ÏP**

**Technical properties**

**Architecture**

Connection system	Typ 2
-------------------	-------

**Functions**

Function access control	Yes
With load management	Yes

**Connectivity**

Number of charging points	1
Number of CEE socket outlets	0
Number of socket outlets GB	0
Number of socket outlets Type 2	1
Number of socket outlets Type 3	0
Number of vehicle connectors CHAdeMO	0
Number of vehicle connectors Type 1	0
Number of vehicle connectors Type 1 CCS	0
Number of vehicle connectors Type 2	0
Number of vehicle connectors Type 2 CCS	0

**Main electrical features**

Nominal voltage	230 V
Frequency	50 Hz
Rated current	32 A

**Dimensions**

Depth of installed product	233 mm
Height of installed product	480 mm
Length	480 mm
Width of installed product	346 mm

**Power**

connected load	8 kW
Max. power per charging point	7.4 kW

**Power supply**

Number of phases for the power supply	1 phase
---------------------------------------	---------

**Materials**

RAL colour	RAL 7035 - Light grey
Material	plastic

Material group other

---

**Scope of delivery**

---

Number of earth leakage circuit breakers  
type A 1

---

**Equipment**

---

With energy meter Yes

---

With house connection box No

---

Number of household socket outlets 1

---

Number of vehicle connectors GB AC 0

---

Number of vehicle connectors GB DC 0

---

With circuit breaker Yes

---

**Standards**

---

European directive RoHs compliant

---

**Safety**

---

Protection index IP IP54

---

REACH conform No

---

Impact strength IK10