



286710

Tronic rotary dimmer, house electronics

Technical characteristics

Architecture

Type of control unit Push & rotative

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Electronic transformers 20...360 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 20...360 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load capacitive

Type of connection with screw terminals

Equipment

Dimming principle phase cut-off

low noise very low noise

Switches / socket outlets with change-over pressure switch

Identification

Application, usage Light control

Main design line Light control

Instructions

