



2874

Tronic rotary dimmer with soft-lock, house electronics

Technical characteristics

Architecture

Type of control unit Push & rotative

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Loss power at full load ≈ 5 W

Electronic transformers 20...525 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 20...525 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load capacitive

Terminal with terminal for base load from mains isolator

Type of connection with plug-in terminals

Equipment

Dimming principle phase cut-off

low noise very low noise

Switches / socket outlets with change-over pressure switch

Use

Identification

Application, usage	Light control
Release issue	2
Main design line	Light control

Instructions

Information text	Trouble-free operation will be obtained only with Berker TronicÂ® transformers.
------------------	---
