



2874

Tronic rotary dimmer with soft-lock, house electronics

Technical characteristics

Architecture

Type of control unit	Push & rotative
----------------------	-----------------

Functions

Soft startup	bulb-preserving soft startup
--------------	------------------------------

Main electrical features

Nominal voltage	230 V
Frequency	50 Hz

Voltage

Operating voltage	230 V AC
Voltage	voltage test possible without dismantling

Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

Dimensions

Axis dimension Ø	4 mm
------------------	------

Power

Loss power at full load	≈ 5 W
Electronic transformers	20...525 W

Materials

Colour	not applicable
Material	Plastic/metal

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	20...525 W
--	------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of load	capacitive
Terminal	with terminal for base load from mains isolator
Type of connection	with plug-in terminals

Equipment

Dimming principle	phase cut-off
-------------------	---------------

low noise	very low noise
Switches / socket outlets	with change-over pressure switch
Use	
Differentiation characteristic 3 - Sales	with soft-lock
Identification	
Application, usage	Light control
Release issue	2
Main design line	Light control
Instructions	
Information text	Trouble-free operation will be obtained only with Berker Tronic® transformers.