



2885

Rotary dimmer with soft-lock house electronics

Technical characteristics

Architecture

Type of control unit	Push & rotative
----------------------	-----------------

Main electrical features

Nominal voltage	230 V
Frequency	50 Hz

Voltage

Operating voltage	230 V AC
-------------------	----------

Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

Dimensions

Axis dimension Ø	4 mm
------------------	------

Power

Loss power at full load	≈ 5 W
-------------------------	-------

Materials

Colour	not applicable
Material	Plastic/metal

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	100...1000 W
--	--------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of load	Resistive load
Type of connection	with screw terminals

Equipment

Dimming principle	phase cut-off
Switches / socket outlets	with change-over pressure switch

Use

Differentiation characteristic 3 - Sales	with soft-lock
--	----------------

Identification

Application, usage	Light control
--------------------	---------------

