



29512089

**LED signal light, RGB, R.1/R.3, p. white glossy**

**Technical characteristics**

**Main electrical features**

|               |          |
|---------------|----------|
| Rated voltage | 230 V AC |
| Frequency     | 50/60 Hz |

**Power**

|                   |  |
|-------------------|--|
| Power consumption | at 195 ... 265 V~, 50/60 Hz - max. 2 W |
|-------------------|--|

**Materials**

|                       |                       |
|-----------------------|-----------------------|
| Colour of design line | polar white           |
| Colour                | white                 |
| RAL colour            | RAL 9010 - Pure white |
| Surface appearance    | glossy                |

**LED control**

|                    |   |
|--------------------|---|
| Quantity LED lamps | 4 |
|--------------------|---|

**Installation, mounting**

|   |                          |
|---|--------------------------|
| For installation in standard wall boxes | according to DIN 49073-1 |
|---|--------------------------|

**Connection**

|                         |                     |
|-------------------------|---------------------|
| Conductor cross-section | 2.5 mm <sup>2</sup> |
|-------------------------|---------------------|

**Settings**

|         |   |
|---------|---|
| Setting | Brightness modifiable via potentiometer |
|---------|---|

**Equipment**

|                           |   |
|---------------------------|---|
| Lighting                  | Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button |
| Switches / socket outlets | colour is switchable via an external switch   |

**Use cases**

|             |               |
|-------------|---------------|
| Application | Light control |
|-------------|---------------|

**temperatur**

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...40 °C |
|---------------------|------------|

**Identification**

|                          |   |
|--------------------------|---|
| Main design line         | Berker R.1/R.3/R.8                                      |
| Secondary design line(s) | Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic |

**Instructions**

Subject to technical modifications

---

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text