



16402079

Relay switch centre plate for hotel card, 1930/R.classic, p. white glossy

Technical characteristics

Architecture

Number of keys	0
----------------	---

Configuration

Switch mode	1pole
-------------	-------

Antibacterial treatment	No
-------------------------	----

Main electrical features

Nominal voltage	230 V
-----------------	-------

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
--	----------

Dimensions

Depth	60 mm
-------	-------

Insertion depth	32 mm
-----------------	-------

Card width	max. 55 mm
------------	------------

Card thickness	0.8...1.2 mm
----------------	--------------

Power

Conventional transformers	1500 VA
---------------------------	---------

Electronic transformers	1500 W
-------------------------	--------

Power consumption	< 0.2 W
-------------------	---------

Materials

Colour of design line	polar white
-----------------------	-------------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Surface appearance	glossy
--------------------	--------

Fluorescent bulbs control

Compact fluorescent lamps	500 W
---------------------------	-------

Fluorescent lamps in duo circuit	1500 W
----------------------------------	--------

LED control

LED	illuminated with blue LED if hotel card is not inserted
-----	---

Incandescent bulbs control

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Screw terminals (max.)	2 x 2,5 mm ²
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

Equipment

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

Centre plates / central plates	with centre plate Ø 58 mm
--------------------------------	---------------------------

Use cases

Application	Light control ; Hotel application
-------------	-----------------------------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Serie 1930/R.classic
------------------	----------------------

Secondary design line(s)	Serie 1930 ; Series R.classic
--------------------------	-------------------------------

Instructions

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--