



16406094

## Relay switch w. centre plate f. hotel card Q.x alu velvety. lacquered

### Technical characteristics

#### Architecture

Number of keys 0

#### Configuration

Switch mode 1pole

Antibacterial treatment No

#### Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

#### Electric current

Inductive load at  $\cos \varphi = 0.6$  max. 6 A

#### Dimensions

Depth 57.3 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

#### Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

#### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

#### Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

#### LED control

LED illuminated with blue LED if hotel card is not inserted

#### Incandescent bulbs control

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Screw terminals (max.)	2 x 2,5 mm <sup>2</sup>
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

**Settings**

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

**Equipment**

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

**Use cases**

Application	Light control ; Hotel application
-------------	-----------------------------------

**Safety**

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

**Use conditions**

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

**Identification**

Application, usage	Light control
--------------------	---------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---