



16406096

Relay switch centre plate for hotel card, Q.x, ant. velvety, lacq.

Technical characteristics

Architecture

Number of keys	0
Fixing mode	flush-mounting

Configuration

Switch mode	1pole
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
Switching current	10 A /230 V AC1

Dimensions

Depth	57.3 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm
Height	71 mm
Width	71 mm

Power

Conventional transformers	1500 VA
Electronic transformers	1500 W

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	velvety

Fluorescent bulbs control

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

LED control

LED	illuminated with blue LED if hotel card is not inserted
-----	---

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	1500 W
--	--------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Screw terminals (max.)	2 x 2,5 mm ²
Type of connection	with screw-in lift terminals

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
Setting	with potentiometer for incremental adjustment of delay time

Scope of delivery

With lamp	No
-----------	----

Equipment

Contact less	No
Lighting	for illumination
Potential-free	with potential-free contact

Use cases

Application	Light control, Hotel application
-------------	----------------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...50 °C
Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage	Light control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9