



303520

## Blind switch 1pole, blind control

### Technical characteristics

#### Architecture

Type of control unit	double rocker
Fixing mode	flush-mounting

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Configuration

Switch mode	with mechanical and electrical interlock to prevent mutual switch-on
-------------	--

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	41.5 mm
Height	70.8 mm
Width	70.8 mm

#### Materials

Material	Plastic/metal
Surface appearance	matt

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Type of connection	with plug-in terminals
--------------------	------------------------

#### Use cases

Application	Blind control
-------------	---------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Identification

