



16406096

Relay switch centre plate for hotel card, Q.x, ant. velvety, lacq.

Technical characteristics

Architecture

Number of keys 0

Configuration

Switch mode 1pole

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$ max. 6 A

Switching current 10 A /230 V AC1

Dimensions

Depth 57.3 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

LED control

LED illuminated with blue LED if hotel card is not inserted

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 1500 W

Installation, mounting

Installation mode with spreader claws

Connection

Screw terminals (max.) 2 x 2,5 mm²

Type of connection with screw-in lift terminals

Settings

Delay time incrementally adjustable 0, 15, 30, 60 s

Setting with potentiometer for incremental adjustment of delay time

Scope of delivery

With lamp No

Equipment

Contact less No

Lighting for illumination

Potential-free with potential-free contact

Use cases

Application Light control ; Hotel application

Safety

REACH conform No

Halogen free No

Use conditions

Operating temperature -5...50 °C

Storage/transport temperature -25...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage Light control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9