



303550

Series switch for hollow-wall mounting, module inserts

Technical characteristics

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode series

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws ; low installation depth ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting	for lighting and monitoring circuit
Heating switch	No
Use cases	
Application	Light control
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Identification	
Application, usage	Light control
Main design line	Light control