


3036



Change-over switch 10AX 250V~, Light control

Technical characteristics

Architecture

Type of control unit single rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode Off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode with spreader claws ; for screw fastening


Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect



Equipment

Lighting for lighting and monitoring circuit

Heating switch No

Use cases

Application Barrier-free application ; HVAC-control ; Light control

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Identification

Application, usage HVAC control ; Light control

Appliance switch type No

Main design line Light control

Instructions

Special note text A control change-over switch is shown here as an example. With 2-pole and 3-pole control on/off switches, other rocker switches and neon lamp units are required.

Information text spreader claws, insulated to the supporting ring, self-resetting