



16408999

## Relay switch centre plate for hotel card, S.1, p. white glossy

### Technical characteristics

#### Architecture

Number of keys 0

#### Configuration

Switch mode 1pole

Antibacterial treatment No

#### Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

#### Electric current

Inductive load at  $\cos \varphi = 0.6$  max. 6 A

Switching current 10 A /230 V AC1

#### Dimensions

Depth 57.3 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Height 71 mm

Width 71 mm

#### Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

#### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

#### Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

#### LED control

LED illuminated with blue LED if hotel card is not inserted

## Incandescent bulbs control

---

230 V incandescent lamps and halogen lamps

1500 W

### Installation, mounting

---

Installation mode with spreader claws

### Connection

---

Screw terminals (max.) 2 x 2,5 mm<sup>2</sup>

Type of connection with screw-in lift terminals

### Settings

---

Delay time incrementally adjustable 0, 15, 30, 60 s

Setting with potentiometer for incremental adjustment of delay time

### Equipment

---

Lighting for illumination

Potential-free with potential-free contact

### Use cases

---

Application Light control ; Hotel application

### Safety

---

REACH conform No

RoHS conform Yes

Halogen free No

### Use conditions

---

Operating temperature -5...50 °C

Storage/transport temperature -25...70 °C (storage at > 45°C reduces the service life)

### Identification

---

Application, usage Light control

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1 ; Berker B.3 ; Berker B.7