



3037

Intermediate switch, light control

Technical characteristics

Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	intermediate
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	42 mm
Insertion depth	32 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1

Type of connection	with plug-in terminals
Type of connection	Quickconnect
Equipment	
Lighting	for lighting and monitoring circuit
Heating switch	No
Use cases	
Application	Barrier-free application, HVAC-control, Light control
Safety	
Protection index IP	IP20
Impact strength	IK07
Identification	
Application, usage	HVAC control, Light control
Appliance switch type	No
Main design line	Light control
Instructions	
Information text	spreader claws, insulated to the supporting ring, self-resetting