



16409906

## Relay switch centre plate for hotel card, S.1/B.3/B.7, ant., matt

### Technical characteristics

#### Architecture

Number of keys	0
----------------	---

#### Configuration

Switch mode	1pole
-------------	-------

Antibacterial treatment	No
-------------------------	----

#### Main electrical features

Nominal voltage	230 V
-----------------	-------

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

#### Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
--	----------

Switching current	10 A /230 V AC1
-------------------	-----------------

#### Dimensions

Depth	57.3 mm
-------	---------

Insertion depth	32 mm
-----------------	-------

Card width	max. 55 mm
------------	------------

Card thickness	0.8...1.2 mm
----------------	--------------

Height	71 mm
--------	-------

Width	71 mm
-------	-------

#### Power

Conventional transformers	1500 VA
---------------------------	---------

Electronic transformers	1500 W
-------------------------	--------

Power consumption	< 0.2 W
-------------------	---------

#### Materials

Colour of design line	anthracite
-----------------------	------------

Surface appearance	matt
--------------------	------

#### Fluorescent bulbs control

Compact fluorescent lamps	500 W
---------------------------	-------

Fluorescent lamps in duo circuit	1500 W
----------------------------------	--------

#### LED control

LED	illuminated with blue LED if hotel card is not inserted
-----	---

#### Incandescent bulbs control

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Screw terminals (max.)	2 x 2,5 mm <sup>2</sup>
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

**Settings**

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

**Equipment**

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

**Use cases**

Application	Light control ; Hotel application
-------------	-----------------------------------

**Safety**

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

**Use conditions**

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

**Identification**

Application, usage	Light control
--------------------	---------------

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7
--------------------------	--------------------------------------