



303808

Double change-over switch, isolated input terminals, light control

Technical characteristics

Architecture

Type of control unit double rocker

Configuration

Switch mode double off/change-over, isolated input terminals

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting for illumination

Heating switch No

Use cases

Application Light control

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Identification

Application, usage Light control

Main design line Light control

Instructions

Information text spreader claws, insulated to the supporting ring, self-resetting